





ON



OFF

2 sec



2 sec






min

max



2 sec



2 sec



2 sec

Change units:

- 0.000 m      0.00 ft
- 0.0000 m    0' 00" 1/32
- 0.000 in     0 in 1/32

# Quick Start

## Leica DISTO™ D2



- 1 Display
- 2 ON/Measure
- 3 Add
- 4 Functions
- 5 Measuring reference
- 6 Clear/OFF
- 7 Memory/Timer
- 8 Bluetooth Smart
- 9 Subtract

- when it has to be right




 2 sec



### Bluetooth® ON/OFF




 Transfer value from main line

 2 sec




### Timer



**FUNC** 2x



### Volume




**FUNC** 2 sec  

**FUNC** 4x




### Pythagoras (3-point)



**1...10**  
8.294 m

### Memory





Clear memory:  
  2 sec

**FUNC** 1x



### Area




**FUNC** 2 sec 

**FUNC** 3x



### Pythagoras (2-point)



**FUNC** 5x



### Stake-out

